

Excellent Integrated System Limited

Stocking Distributor

Click to view price, real time Inventory, Delivery & Lifecycle Information:

[ASSMANN WSW Components](#)
[AK-ESATA-SATA100](#)

For any questions, you can email us directly:

sales@integrated-circuit.com

	1	2	3	4	5	6	7																																												
A							A																																												
B							B																																												
C							C																																												
D							D																																												
E							E																																												
F	<p>Material:</p> <ul style="list-style-type: none"> Cable: UL2725 [26AWG(1/0.404)*2F INS:HD-PE+D/W(1/0.32)*2C+AL/MY]*2F <ul style="list-style-type: none"> - Inner Jacket PVC Black - OD 2.1*7.3MM +Braid(16/10/0.1)+PVC Jacket Color: Black OD 4.0*9.0MM P1 Connector: eSATA 7P/F Crimp Type <ul style="list-style-type: none"> - Top/Bottom metal shell plate nickel - Pin G/F - Insulator Black P2 Connector: SATA 7P/F Crimp Type <ul style="list-style-type: none"> - Top/Bottom metal shell plate nickel - Pin G/F - Insulator Black Tube: Heat shrink tube Black OD 12MM L 10MM Acetate: Acetate cloth tape W 10MM * L 40MM Copper Foil: Double-Sided conductive copper foil 20μ" W 10MM*L 30MM Outer Jacket: PVC 45P Color Black <p>Electrical:</p> <ul style="list-style-type: none"> 100% Open Short & Miswire test Conductive resistance: 1Ω Max. Insulation Resistance: 10MΩ/Min. Hi-Pat Test 300V DC <p style="text-align:right;">Unit: MM</p>						F																																												
G	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td>Scale</td> <td>1:1</td> <td></td> <td></td> <td></td> <td></td> <td>Name</td> <td rowspan="5" style="vertical-align: top;"> Item No. AK-ESATA-SATA100 </td> </tr> <tr> <td colspan="2">TOLERANCE</td> <td></td> <td></td> <td></td> <td>Drawn</td> <td>12.29.11</td> <td rowspan="2">Chappell</td> </tr> <tr> <td>X.X</td> <td>±0.40</td> <td></td> <td></td> <td></td> <td>Approved</td> <td></td> </tr> <tr> <td>X.XX</td> <td>±0.25</td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>X.XXX</td> <td>±0.15</td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>Angle</td> <td>±3°</td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> </table>						Scale	1:1					Name	Item No. AK-ESATA-SATA100	TOLERANCE					Drawn	12.29.11	Chappell	X.X	±0.40				Approved		X.XX	±0.25						X.XXX	±0.15						Angle	±3°						G
Scale	1:1					Name	Item No. AK-ESATA-SATA100																																												
TOLERANCE					Drawn	12.29.11		Chappell																																											
X.X	±0.40				Approved																																														
X.XX	±0.25																																																		
X.XXX	±0.15																																																		
Angle	±3°																																																		
H							H																																												
H							H																																												
H	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width:33%;">Modification</td> <td style="width:16.5%;">Date</td> <td style="width:16.5%;">Name</td> <td style="width:16.5%;"></td> <td style="width:16.5%;"></td> <td style="width:16.5%;"></td> <td style="width:16.5%;"></td> <td style="width:16.5%;"></td> </tr> </table>						Modification	Date	Name						H																																				
Modification	Date	Name																																																	
H	1	2	3	4	5	6	7	H																																											

