

Excellent Integrated System Limited

Stocking Distributor

Click to view price, real time Inventory, Delivery & Lifecycle Information:

[Desco](#)
[63110](#)

For any questions, you can email us directly:

sales@integrated-circuit.com



SPI

- Medical grade stainless steel interior expansion band will not cause allergic skin reactions for most people
- Non-flaking or scratching laminated insulator on all external surfaces protects wearers from electrical hazards
- Superior contact with skin with more reliable path-to-ground
- Designed to be used with Dual-Wire Coil Cords and Dual-Wire Continuous Monitors
- Available in large, medium or small sizes
- 7mm sockets

ITEM	DESCRIPTION	CIRCUMFERENCE	
		MIN	MAX
63208	Dual-wire Metal Wristband only, 7mm sockets, M	6" (152.4mm)	11" (279.4mm)
63210	Dual-wire Metal Wristband only, 7mm sockets, S	5.5" (139.7mm)	9" (228.6mm)
63110	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 7 mm sockets, L	7" (177.8mm)	12" (304.8mm)
63112	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 7 mm sockets, M	6" (152.4mm)	11" (279.4mm)
63114	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 7 mm sockets, S	5.5" (139.7mm)	9" (228.6mm)
63131	Dual-wire Metal Wrist Strap, with 12' Coil Cord, 7 mm sockets, M	6" (152.4mm)	11" (279.4mm)
63132	Dual-wire Metal Wrist Strap, with 12' Coil Cord, 7 mm sockets, S	5.5" (139.7mm)	9" (228.6mm)

"Typical test programs recommend that wrist straps that are used daily should be tested daily. However, if the products that are being produced are of such value that knowledge of a continuous, reliable ground is needed, and then continuous monitoring should be considered or even required." (ESD Handbook TR 20.20 section 5.3.2.4.4)

"All personnel shall be bonded or electrically connected to the grounding / equipotential bonding system when handling ESDS [ESD sensitive] items." (ANSI/ESDS20.20-2007 section 8.1)

"When personnel are seated at ESD protective workstations, they shall be connected to the grounding / equipotential bonding system via a wrist strap system." (ANSI/ESDS20.20-2007 section 8.2)

See drawing 63488 for coil cord details.



SEMTRONICS WRISTBAND, DUAL, METAL, 7MM SOCKET

ESD SYSTEMS.com

ESD SYSTEMS.COM
432 NORTHBORO ROAD CENTRAL
MARLBORO, MA 01752 USA
TEL. (508) 485-7390 FAX (508) 480-0257



Visit our online
library of Tech Drawings:
ESDSystems.com

**DRAWING
63208**

**DATE:
October
2008**