

## **Excellent Integrated System Limited**

Stocking Distributor

Click to view price, real time Inventory, Delivery & Lifecycle Information:

[Desco](#)  
[63230](#)

For any questions, you can email us directly:

[sales@integrated-circuit.com](mailto:sales@integrated-circuit.com)



- Medical grade stainless steel interior expansion band will not cause allergic skin reactions for most people
- Non-flaking or scratching laminated insulator on all external surfaces protects wearers from electrical hazards
- Superior contact with skin with more reliable path-to-ground
- Designed to be used with Dual-Wire Coil Cords and Dual-Wire Continuous Monitors
- Available in large, medium, or small sizes
- 4mm studs

ITEM	DESCRIPTION	CIRCUMEFERENCE	
		MIN	MAX
63220	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 4 mm studs, L	7" (177.8mm)	12" (304.8mm)
63221	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 4 mm studs, M	6" (152.4mm)	11" (279.4mm)
63222	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 4 mm studs, S	5.5" (139.7mm)	9" (228.6mm)
63230	Dual-wire Metal Wrist Strap, with 12' Coil Cord, 4 mm studs, L	7" (177.8mm)	12" (304.8mm)
63231	Dual-wire Metal Wrist Strap, with 12' Coil Cord, 4 mm studs, M	6" (152.4mm)	11" (279.4mm)
63232	Dual-wire Metal Wrist Strap, with 12' Coil Cord, 4 mm studs, S	5.5" (139.7mm)	9" (228.6mm)

"Typical test programs recommend that wrist straps that are used daily should be tested daily. However, if the products that are being produced are of such value that knowledge of a continuous, reliable ground is needed, and then continuous monitoring should be considered or even required." (ESD Handbook TR 20.20 section 5.3.2.4.4)

"All personnel shall be bonded or electrically connected to the grounding / equipotential bonding system when handling ESDS [ESD sensitive] items." (ANSI/ESDS20.20-2007 section 8.1)

"When personnel are seated at ESD protective workstations, they shall be connected to the grounding / equipotential bonding system via a wrist strap system." (ANSI/ESDS20.20-2007 section 8.2)

See drawing 63500 for cord details



**SEMTRONICS WRISTBAND, DUAL, METAL, 4MM SOCKET**

**ESD SYSTEMS.com**

ESD SYSTEMS.COM  
432 NORTHBORO ROAD CENTRAL  
MARLBORO, MA 01752 USA  
TEL. (508) 485-7390 FAX (508) 480-0257



Visit our online  
library of Tech Drawings:  
ESDSYSTEMS.com

**DRAWING  
63220**

**DATE:  
October  
2008**